51 mm (2") photomultiplier 9829B series data sheet



1 description

The 9829B is a 51 mm (2") diameter, end window photomultiplier with a thin domed window, sandblasted for enhanced cathode sensitivity, blue-green sensitive bialkali photocathode and 12 BeCu dynodes of linear focused design for good linearity and timing. The 9829QB is a variant for applications requiring uv sensitivity.

2 applications

- liquid scintillation counting
- · photon counting of bio- and chemi-luminescent samples
- · low light level detection

3 features


good SER

4 window characteristics

	9829B borosilicate	9829QB* fused silica
spectral range**(nm) refractive index (n _d)	290 - 630 1.49	160 - 630 1.46
K (ppm) Th (ppb) U (ppb)	300 250 100	<10 <10 <10

*note that the sidewall contains graded seals of high K content
**wavelength range over which quantum efficiency exceeds 1 % of peak

5 typical spectral response curves




6 characteristics

				max
photocathode: bialkali active diameter quantum efficiency at peak luminous sensitivity with CB filter with CR filter dynodes: 12LFBeCu anode sensitivity in divider A:	mm % µA/Im	9.5	46 30 85 12.5 2	
nominal anode sensitivity max. rated anode sensitivity overall V for nominal A/Im overall V for max. rated A/Im	A/Im A/Im V V		500 2000 1600 1800	1900
gain at nominal A/Im dark current at 20 °C: dc at nominal A/Im dc at max. rated A/Im dark count rate	x 10 ⁶ nA nA s ⁻¹		6 3 12 300	10
pulsed linearity (-5% deviation) divider A divider B rate effect (I _a for ∆g/g=1%):			50 150 1	
magnetic field sensitivity: the field for which the output decreases by 50 % most sensitive direction	T x 10 ⁻⁴		1	
temperature coefficient: timing:	% °C ⁻¹		± 0.5	
single electron rise time single electron fwhm single electron jitter (fwhm) multi electron rise time multi electron fwhm transit time weight:	ns ns ns ns ns ns		2 3 2.2 3.2 4.5 41 130	
maximum ratings: anode current cathode current gain sensitivity temperature	μΑ nA x 10 ⁶ A/lm °C	-30		100 100 25 2000 60
V (k-a) ⁽¹⁾ V (k-d1) V (d-d) ⁽²⁾ ambient pressure (absolute)	V V V kPa			2800 500 450 202

subject to not exceeding max. rated sensitivity (2) subject to not exceeding max rated V(k-a)

7 typical voltage gain characteristics




8 voltage divider distribution

Α	300\	/ R	2	 R	R	R	R	R	R	Standard
В	300\	/ R	2	 R	R 1	I.25R 1	1.5R	2R	3R	High Pulsed Linearity


note: focus connected to d₁

Characteristics contained in this data sheet refer to divider A unless stated otherwise.

9 external dimensions mm



10 base configuration (viewed from below)




Our range of B21 sockets, available for this series, includes versions with or without a mounting flange, and versions with contacts for mounting directly onto printed circuit boards.

11 handling instructions

The window of this pmt has been specially cleaned to give maximum efficiency. It should not be touched with fingers or allowed to come into contact with oil or grease. The window can be cleaned with isopropyl alcohol to remove oil deposits.

12 ordering information

The 9829B meets the specification given in this data sheet. You may order **variants** by adding a suffix to the type number. You may also order **options** by adding a suffix to the type number. You may order product with **specification options** by discussing your requirements with us. If your selection option is for one-off order, then the product will be referred to as 9829A. For a repeat order, **ET Enterprises** will give the product a two digit suffix after the letter B, for example B21. This identifies your specific requirement.



14 voltage dividers

The standard voltage dividers available for these pmts are tabulated below:

						d ₁₀ d	l ₁₁ d		
C628A	3R	R	R	 R	R	R	R	R	
C628B	3R	R	R	 R	1.25F	1.5R	2R	3R	
C628C	300 V	R	R	 R	R	R	R	R	
C628D	300 V	R	R	 R	1.25F	1.5R	2R	3R	

note: focus connected to d₁

 $R = 330 \text{ k}\Omega$

*mumetal is a registered trademark of Magnetic Shield Corporation

ET Enterprises Limited 45 Riverside Way Uxbridge UB8 2YF United Kingdom tel: +44 (0) 1895 200880

tel: +44 (0) 1895 200880 fax: +44 (0) 1895 270873 e-mail: sales@et-enterprises.com web site: www.et-enterprises.com

ADIT Electron Tubes

300 Crane Street Sweetwater TX 79556 USA tel: (325) 235 1418 toll free: (800) 521 8382 fax: (325) 235 2872

e-mail: sales@electrontubes.com
web site: www.electrontubes.com

choose accessories for this pmt on our website

an ISO 9001 registered company

The company reserves the right to modify these designs and specifications without notice. Developmental devices are intended for evaluation and no obligation is assumed for future manufacture. While every effort is made to ensure accuracy of published information the company cannot be held responsible for errors or consequences arising therefrom.



© ET Enterprises Ltd, 2010 DS_ 9829B Issue 8 (21/09/10)