
509/22 nm BrightLine® single-band bandpass filter

Part Number: FF01-509/22-25





Semrock, Inc

3625 Buffalo Road, Suite 6 Rochester, New York 14624

Main Phone: +1 585.594.7050 (worldwide)
Toll Free Phone: 866.736.7625 (866-SEMROCK)
(within US and Canada)

Your filter spectrum may differ slightly from the typical spectrum above, but is certified to meet the optical specifications noted below.



509/22 nm BrightLine® single-band bandpass filter

Individual fluorescence bandpass filters that have been optimized for use in a variety of fluorescence instruments. All thin-film, hard-coated construction for unsurpassed performance and reliability.

Part Number	Size	Price1	Stock Status
FF01-509/22-25	25 mm x 5.0 mm	\$355	In Stock
FF01-509/22-25-STR	25 mm threaded ring for Sutter Lambda filter wheel	\$375	2nd Day Ship
FF01-509/22-32	32 mm x 5.0 mm	\$582	Contact Us
FF01-509/22-21.8-D	21.8 mm x 2.0 mm (unmounted)	\$355	Contact Us

Don't see a size you need? Contact us for custom sizing - available in less than a week (sizing fee applies).

1) US domestic pricing only. If you are ordering from outside the US, please contact your nearest regional distributor for the correct list price.

Optical Specifications

Specification	Value
Transmission Band 1	Tavg > 93% 497.6 - 519.5 nm
Center Wavelength 1	508.6 nm
Guaranteed Minimum Bandwidth 1	21.9 nm
FWHM Bandwidth 1 (nominal)	26.1 nm
Blocking Band 1	ODavg > 5 200 - 300 nm
Blocking Band 2	ODavg > 6 300 - 486 nm
Blocking Band 3	ODavg > 8 464 - 486 nm (Design specification - measurements are noise-floor limited)
Blocking Band 4	OD > 3.5 491.8 nm
Blocking Band 5	OD > 3.5 525.8 nm
Blocking Band 6	ODavg > 8 532 - 554 nm (Design specification - measurements are noise-floor limited)
Blocking Band 7	ODavg > 8 603 - 800 nm (Design specification - measurements are noise-floor limited)
Blocking Band 8	ODavg > 6 554 – 850 nm
Blocking Band 9	ODavg > 4 850 - 925 nm
Blocking Band 10	ODavg > 2 925 - 1100 nm
Blocking Band 11	

General Filter Specifications

Specification	Value	
Angle of Incidence	0 ± 5 degrees	
Cone Half-angle	7 degrees	
0 :: 10	Testing has proven to show no signs of degradation when exposed to at least 6.0 W of power from an unfiltered	

xenon arc lamp over a 25 mm diameter (corresponding to 1.2 W/cm²) for over 500 hrs.

Effective Index 2.04

Physical Filter Specifications (applies to standard sized parts; contact us regarding other sizes)

Specification	Value
Transverse Dimensions (Diameter)	25 mm
Transverse Tolerance (mounted)	+ 0.0 / – 0.1 mm
Filter Thickness (Mounted)	5.0 mm
Filter Thickness Tolerance (Mounted)	± 0.1 mm
Clear Aperture	≥ 21 mm
Scratch-Dig	60-40
Substrate Thickness (unmounted)	2.0 mm
Substrate Thickness Tolerance (unmounted)	± 0.1 mm
Orientation	Arrow on ring indicates preferred direction of propagation of light