


## 575/25 nm BrightLine® single-band bandpass filter

Part Number: FF03-575/25-25



**Semrock**  
A Unit of **IPXX** Corporation

### Semrock, Inc

3625 Buffalo Road, Suite 6  
Rochester, New York 14624

Main Phone: +1 585.594.7050 (worldwide)  
Toll Free Phone: 866.736.7625 (866-SEMROCK)  
(within US and Canada)

Your filter spectrum may differ slightly from the typical spectrum above, but is certified to meet the optical specifications noted below.



### 575/25 nm BrightLine® single-band bandpass filter

Individual fluorescence bandpass filters that have been optimized for use in a variety of fluorescence instruments. All thin-film, hard-coated construction for unsurpassed performance and reliability.

Part Number	Size	Price <sup>1</sup>	Stock Status
FF03-575/25-25	25 mm x 5.0 mm	\$305	In Stock
FF03-575/25-25-STR	25 mm threaded ring for Sutter Lambda filter wheel	\$325	2nd Day Ship
FF03-575/25-32	32 mm x 5.0 mm	\$500	In Stock

Don't see a size you need? Contact us for custom sizing – available in less than a week (sizing fee applies).

1) US domestic pricing only. If you are ordering from outside the US, please contact your nearest [regional distributor](#) for the correct list price.

### Optical Specifications

Specification	Value
Transmission Band 1	T <sub>avg</sub> > 93% 562.5 – 587.5 nm
Center Wavelength 1	575 nm
Guaranteed Minimum Bandwidth 1	25 nm
FWHM Bandwidth 1 (nominal)	31.3 nm
Blocking Band 1	OD <sub>avg</sub> > 6 300 – 547 nm
Blocking Band 2	OD > 0.4 554.5 nm
Blocking Band 3	OD > 3.5 552.5 nm
Blocking Band 4	OD > 3.5 596.5 nm
Blocking Band 5	OD <sub>avg</sub> > 5 601 – 610 nm
Blocking Band 6	OD <sub>avg</sub> > 6 612 – 638 nm
Blocking Band 7	OD <sub>avg</sub> > 6 640 – 700 nm
Blocking Band 8	OD <sub>avg</sub> > 5.5 700 – 925 nm
Blocking Band 9	OD <sub>avg</sub> > 4 925 – 1200 nm

### General Filter Specifications

Specification	Value
Angle of Incidence	0 ± 5 degrees
Cone Half-angle	7 degrees
Optical Damage Rating	Testing has proven to show no signs of degradation when exposed to at least 6.0 W of power from an unfiltered xenon arc lamp over a 25 mm diameter (corresponding to 1.2W/cm <sup>2</sup> ) for over 500 hrs.
Effective Index	1.83

### Physical Filter Specifications (applies to standard sized parts; contact us regarding other sizes)

[www.Semrock.com/FilterDetails.aspx?id=FF03-575/25-25](http://www.Semrock.com/FilterDetails.aspx?id=FF03-575/25-25)

Specification	Value
Transverse Dimensions (Diameter)	25 mm
Transverse Tolerance (mounted)	+ 0.0 / - 0.1 mm
Filter Thickness (Mounted)	5.0 mm
Filter Thickness Tolerance (Mounted)	± 0.1 mm
Clear Aperture	≥ 21 mm
Scratch-Dig	60-40
Substrate Thickness (unmounted)	2.0 mm
Substrate Thickness Tolerance (unmounted)	± 0.1 mm
Orientation	Arrow on ring indicates preferred direction of propagation of light