
# 475/28 nm BrightLine® single-band bandpass filter

# Part Number: FITC-Ex01-Clin-25





### Semrock, Inc

3625 Buffalo Road, Suite 6 Rochester, New York 14624

Main Phone: +1 585.594.7050 (worldwide)
Toll Free Phone: 866.736.7625 (866-SEMROCK)
(within US and Canada)

Your filter spectrum may differ slightly from the typical spectrum above, but is certified to meet the optical specifications noted below.



#### 475/28 nm BrightLine® single-band bandpass filter

Individual fluorescence bandpass filters that have been optimized for use in a variety of fluorescence instruments. All thin-film, hard-coated construction for unsurpassed performance and reliability.

Part Number	Size	Price1	Stock Status
FITC-Ex01-Clin-25	25 mm x 5.0 mm	\$305	In Stock
FITC-Ex01-Clin-21.8-D	21.8 mm x 2.0 mm (unmounted)	\$305	2nd Day Ship

This part is not available for custom sizing.

1) US domestic pricing only. If you are ordering from outside the US, please contact your nearest regional distributor for the correct list price.

## **Optical Specifications**

Specification	Value
Transmission Band 1	Tavg > 90% 461 – 489 nm
Center Wavelength 1	475 nm
Guaranteed Minimum Bandwidth 1	28 nm
FWHM Bandwidth 1 (nominal)	32 nm
Blocking Band 1	ODavg > 5 200 – 449 nm
Blocking Band 2	ODavg > 5 500.5 - 500.5 nm
Blocking Band 3	ODavg > 10 515 - 570 nm (Design specification - measurements are noise-floor limited)
Blocking Band 4	ODavg > 5 570 – 700 nm
Blocking Band 5	ODavg > 2.5 700 - 925 nm
Blocking Band 6	ODavg > 2 925 - 1100 nm

#### **General Filter Specifications**

Specification	Value Value	
Angle of Incidence	0 ± 5 degrees	
Cone Half-angle	7 degrees	
Optical Damage Rating	Testing has proven to show no signs of degradation when exposed to at least 6.0 W of power from an unfiltered xenon arc lamp over a 25 mm diameter (corresponding to 1.2 W/cm²) for over 500 hrs.	
Effective Index	1.92	

## Physical Filter Specifications (applies to standard sized parts; contact us regarding other sizes)

Specification	Value	
Transverse Dimensions (Diameter)	25 mm	
Transverse Tolerance (mounted)	+ 0.0 / - 0.1 mm	

Filter Thickness (Mounted)	5.0 mm	
Filter Thickness Tolerance (Mounted)	± 0.1 mm	
Clear Aperture	≥ 21 mm	
Scratch-Dig	60-40	
Substrate Thickness (unmounted)	2.0 mm	
Substrate Thickness Tolerance (unmounted)	± 0.1 mm	
Orientation	Arrow on ring indicates preferred direction of propagation of light	