


## 433/530 nmBrightLine® dual-band bandpass filter

Part Number: FF01-433/530-25



### Semrock, Inc

3625 Buffalo Road, Suite 6  
 Rochester, New York 14624

Main Phone: +1 585.594.7050 (worldwide)  
 Toll Free Phone: 866.736.7625 (866-SEMROCK)  
 (within US and Canada)

Your filter spectrum may differ slightly from the typical spectrum above, but is certified to meet the optical specifications noted below.



### 433/530 nmBrightLine® dual-band bandpass filter

Individual multiband fluorescence bandpass filters that utilize Semrock's patented single-substrate construction. These filters have extremely high transmission, steep and well-defined edges, and outstanding blocking between the passbands. All thin-film, hard-coated construction for unsurpassed performance and reliability.

Part Number	Size	Price <sup>1</sup>	Stock Status
FF01-433/530-25	25 mm x 3.5 mm	\$395	In Stock
FF01-433/530-23.3-D	23.3 mm x 2.0 mm (unmounted)	\$395	2nd Day Ship

Don't see a size you need? Contact us for custom sizing – available in less than a week (sizing fee applies).

<sup>1</sup> US domestic pricing only. If you are ordering from outside the US, please contact your nearest [regional distributor](#) for the correct list price.

### Optical Specifications

Specification	Value
Transmission Band 1	T <sub>avg</sub> > 90% 414 – 452 nm
Center Wavelength 1	433 nm
Guaranteed Minimum Bandwidth 1	38 nm
FWHM Bandwidth 1 (nominal)	43.2 nm
Transmission Band 2	T <sub>avg</sub> > 90% 510 – 550 nm
Center Wavelength 2	530 nm
Guaranteed Minimum Bandwidth 2	40 nm
FWHM Bandwidth 2 (nominal)	47.4 nm
Blocking Band 1	OD <sub>avg</sub> > 6 300 – 393 nm
Blocking Band 2	OD > 3.5 403.5 nm
Blocking Band 3	OD > 3.5 459 nm
Blocking Band 4	OD <sub>avg</sub> > 6 466 – 495 nm
Blocking Band 5	OD > 3.5 502.5 nm
Blocking Band 6	OD <sub>avg</sub> > 6 565.5 – 750 nm
Blocking Band 7	OD <sub>avg</sub> > 6 750 – 925 nm

### General Filter Specifications

Specification	Value
Angle of Incidence	0 ± 5 degrees
Cone Half-angle	7 degrees
Optical Damage Rating	Testing has proven to show no signs of degradation when exposed to at least 6.0 W of power from an unfiltered xenon arc lamp over a 25 mm diameter (corresponding to 1.2 W/cm <sup>2</sup> ) for over 500 hrs.
Effective Index	2.06

**Physical Filter Specifications (applies to standard sized parts; contact us regarding other sizes)**

Specification	Value
Transverse Dimensions (Diameter)	25 mm
Transverse Tolerance (mounted)	+ 0.0 / - 0.1 mm
Filter Thickness (Mounted)	3.5 mm
Filter Thickness Tolerance (Mounted)	± 0.1 mm
Clear Aperture	≥ 22 mm
Scratch-Dig	60-40
Substrate Thickness (unmounted)	2.0 mm
Substrate Thickness Tolerance (unmounted)	± 0.1 mm
Orientation	Arrow on ring indicates preferred direction of propagation of light